

Motor-drive Air Pump Series


MX-808ST-S

- Gas analysis equipment
- Gas detectors




Maximum flow rate	Greater than or equal to L/min	25.0
	Greater than or equal to cfm	0.88
Maximum discharge pressure	Greater than or equal to kPa	147.0
	Greater than or equal to psi	21.38
Maximum vacuum	Not greater than kPa	-59.9
	Not greater than in.Hg	-17.68
Voltage	V	AC100
Current	A	1.00
Insulation class		E
Ambient temperature	°C	0-40
Gas contact material		PTFE,SUS316,SUS304
Connection		Rc1/4
Mass	kg	5.00

*This website contains only a representative part of our product line-up. We also have pumps, in addition to the list below, that can meet a customer's specific requirements regarding flow rate, pressure, variable voltage and gas contact materials. Please feel free to contact us to discuss your needs.



Characteristic Curve



Motor-drive Air Pump Series


MX-808ST-W

- Radiation measuring devices
- Gas analysis equipment
- Gas detectors
- Automobile emission measuring equipment



Maximum flow rate	Greater than or equal to L/min	25.0 × 2
	Greater than or equal to cfm	0.88 × 2
Maximum discharge pressure	Greater than or equal to kPa	147.0
	Greater than or equal to psi	21.38
Maximum vacuum	Not greater than kPa	-59.9
	Not greater than in.Hg	-17.68
Voltage	V	AC100
Current	A	1.00
Insulation class		E
Ambient temperature	°C	0-40
Gas contact material		PTFE,SUS304,SUS316
Connection		Rc1/4
Mass	kg	6.00

*This website contains only a representative part of our product line-up. We also have pumps, in addition to the list below, that can meet a customer's specific requirements regarding flow rate, pressure, variable voltage and gas contact materials. Please feel free to contact us to discuss your needs.



Characteristic Curve

